



YS44FXLTCKITC, Compression Splice Kit with Clear Heat Shrink, 750 kcmil G,H, 777 DLO, Cu

By Burndy
Catalog # [YS44FXLTCKITC](#)

750 kcmil G,H,777 DLO, CU, SPLICE KIT with Clear Heat Shrink

Features

- In-line splice kit includes compression splice connector and heat shrink
- Barrel is designed with internal chamfer at the wire entry to ensure smooth insertion of wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	750 kcmil G,H,777 DLO
Conductor - Copper Flex K Size A	750 kcmil
Conductor - Copper Flex K Size B	750 kcmil
Conductor - Copper Flex M Size B	750 kcmil
Conductor - AL Str Size Range	777 kcmil
Conductor - Copper Flex M Size A	750 kcmil
Conductor - Copper Str Size	750 Kcmil
Conductor - Copper Flex I Size B	750 kcmil
Conductor - Copper Flex I Size Range	750 kcmil
Conductor - Copper Flex G Size A	750 kcmil
Conductor - Copper Flex G Size B	750 kcmil



Conductor - Copper DLO Size Range	777 kcmil
Conductor Size	750 KCMIL
Conductor - Copper Flex H Size A	750 kcmil
Conductor - Copper Flex G Size Range	750 kcmil
Conductor Type	FLEX
Conductor - Copper Str Size Range	750 kcmil
Conductor - Copper Flex H Size B	750 kcmil
Conductor - Copper Flex H Size Range	750 kcmil
Conductor - Copper Flex I Size A	750 kcmil

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	122.17 mm
Dimension - Strip Length inch	1.96
Dimension - B Length inch	1.96 in
Dimension - Length BB inch	1.96 in
Dimension - Length Overall inch	4.81 in

General

Trade Name	HYLINK™
Die Index	L115
Die Index Run Side	L115
Die Index Tap Side	L115
Color	Yellow
Feature - Barrel Type	Standard
Feature - Barrel Style	Skived

Plated	Y
Color Code	Yellow
UPC	781810343951
Color Code - Side B	Yellow
Color Code - Side A	Yellow
Type	YS-TC
Construction Material - Main	Copper
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810343951
UPC 14 Digit GTIN	00781810343951

Logistics

Minimum Pack Quantity	1
Pallet Quantity	900
Carton Quantity	10

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand