



YS44L, Compression Splice, 1000 kcmil Cu, Standard Barrel

By Burndy
Catalog # [YS44L](#)

1000 kcmil, CU, Standard Barrel SPLICE



Features

- Copper seamless barrel with center stop indentations to indicate when wire is fully inserted into each side of the barrel
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Splice

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	1000 kcmil
Conductor - Copper Str Size	1000 kcmil
Conductor - Copper Str	1000
Compact Size	
Conductor Size	1000 KCMIL
Conductor Type	CODE
Conductor - Copper Str Size Range	1000 kcmil

Configuration

Connector Type	STANDARD BARREL
----------------	-----------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	109 mm
Dimension - Strip Length inch	1-15/16
Dimension - B Length fraction	1-7/8 in
Dimension - B Length inch	1.88 in
Dimension - Length Overall inch	4.28 in

General

Trade Name	HYLINK™
Die Index	27
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	White
UPC	781810527757
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810527757
UPC 14 Digit GTIN	00781810527757

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2304
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)