



Compression Splice

By Burndy
Catalog # [YS44LFX](#)

Copper Compression Splice



Features

- Copper Compression Splice
- Standard Barrel with Internal Chamfer

Application

Wire Splice

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer NO
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	CSA

Conductor

Conductor - Copper Flex G Size	750 KCMIL
Conductor - Copper DLO Size	777 KCMIL
Range	
Conductor - Copper DLO Size	777 DLO
Conductor Size	750 KCMIL
Conductor - Copper Flex H Size	750 KCMIL
Conductor - Copper Flex G Size	750 KCMIL
Range	
Conductor - Material	COPPER
Wire Size	750 KCMIL
Conductor Type	FLEX
Conductor - Copper Str Size	750 KCMIL
Conductor - Copper Flex H Size	750 KCMIL
Range	
Conductor - Copper Flex I Size	750 KCMIL

Conductor - Copper Flex I Size 750 KCMIL
Range

Configuration

Connector Type STANDARD BARREL

Current

Voltage Rating 35 kV

Dimensions

Length 4.28 in
Dimension - B Length inch 1.81

General

Color Code	Yellow
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	L115
UPC	621945623897
Type	YS
Construction Material - Main	Copper
Material	COPPER
Finish Type	Tin-Plated

Logistics

Pallet Quantity 2304
Carton Quantity 4

Product Assets

[Catalog \[English\]](#)