



YS4CFXLTKITC, Compression Splice Kit with Clear Heat Shrink, 4 Flex G,H,I,K,M, DLO, 4 AWG Cu

By Burndy
Catalog # YS4CFXLTKITC

4 Flex G,H,I,K,M,DLO, 4 AWG, CU, SPLICE KIT with Clear Heat Shrink

Features

- In-line splice kit includes compression splice connector and heat shrink
- Barrel is designed with internal chamfer at the wire entry to ensure smooth insertion of wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Splice

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	4 AWG
Conductor - Copper Flex K Size Range	4 AWG
Conductor - Copper Flex K Size	4 AWG
Conductor - Copper Flex M Size Range	4 AWG
Conductor - Copper Flex M Size	4 AWG
Conductor - Copper Str Size	4 AWG
Conductor - Copper Flex I Size Range	4 AWG
Conductor - Copper Flex G Size	4 AWG
Conductor - Copper DLO Size Range	4 AWG
Conductor - Copper DLO Size	4 AWG
Conductor Size	4 AWG
Conductor - Copper Flex H Size	4 AWG



Conductor - Copper Flex G Size Range	4 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size Range	4 AWG
Conductor - Copper Flex H Size Range	4 AWG
Conductor - Copper Flex I Size	4 AWG

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	42.92 mm
Dimension - Strip Length inch	11/16
Dimension - B Length inch	0.74 in
Dimension - Length BB inch	0.74 in
Dimension - Length Overall inch	1.69 in

General

Trade Name	HYLINK™
Die Index	8
Feature - Barrel Type	Standard
Feature - Barrel Style	Skived
Plated	Y
Color Code	Gray
UPC	781810346402
Type	YS-TC
Construction Material - Main Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810346402
UPC 14 Digit GTIN	00781810346402

Logistics

Minimum Pack Quantity	12
Pallet Quantity	3600
Carton Quantity	25

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand