



YS5CLBOX, Compression Splice, 5 AWG Cu, Standard Barrel

By Burndy
Catalog # [YS5CLBOX](#)

5 AWG, CU, Standard Barrel SPLICE



Features

- Copper seamless barrel with center stop indentations to indicate when wire is fully inserted into each side of the barrel
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Splice

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Material	COPPER
Wire Size	#5 AWG
Conductor - Copper Str Size	5 AWG
Conductor Size	5 AWG
Conductor - Copper Str Navy Size	30 (19) Navy
Conductor Type	CODE
Conductor - Copper Str Size Range	5 AWG

Configuration

Connector Type	STANDARD BARREL
----------------	-----------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	48 mm
Dimension - Outside Diameter inch	0.30 in
Dimension - Strip Length inch	7/8
Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.81 in
Dimension - Length Overall inch	1.90 in

General

Trade Name	HYLINK™
Die Index	7
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Blue
UPC	781810555606
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810555606
UPC 14 Digit GTIN	00781810555606

Logistics

Minimum Pack Quantity	50
Carton Quantity	50

Product Assets

[Catalog \[English\]](#)