



YS8CFXLTCKITC, Compression Splice Kit with Clear Heat Shrink, 8 Flex G,H,I,K,M, DLO, 8 AWG, Cu

By Burndy
Catalog # [YS8CFXLTCKITC](#)

8 Flex G,H,I,K,M,DLO, 8 AWG, CU, SPLICE KIT with Clear Heat Shrink

Features

- In-line splice kit includes compression splice connector and heat shrink
- Barrel is designed with internal chamfer at the wire entry to ensure smooth insertion of wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Splice

Specifications

Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes
Conductor	
Conductor - Copper Flex G Size	8 AWG
Conductor - Copper DLO Size	8 AWG
Range	
Conductor - Copper DLO Size	8 AWG
Conductor Size	8 AWG
Conductor - Copper Flex H Size	8 AWG
Conductor - Copper Flex G Size	8 AWG
Range	
Conductor - Material	COPPER
Wire Size	8 AWG
Conductor - Copper Flex K Size	8 AWG
Range	
Conductor - Copper Flex K Size	8 AWG
Conductor - Copper Flex M Size	8 AWG
Range	
Conductor - Copper Flex M Size	8 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	8 AWG
Range	
Conductor - Copper Str Size	8 AWG
Conductor - Copper Flex H Size	8 AWG
Range	
Conductor - Copper Flex I Size	8 AWG
Conductor - Copper Flex I Size	8 AWG
Range	



Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	38 mm
Dimension - B Length inch	0.65 in
Dimension - Length BB inch	0.65 in
Dimension - Length Overall inch	1.48 in
Dimension - Strip Length inch	5/8

General

Feature - Barrel Type	Standard
Feature - Barrel Style	Skived
Plated	Y
Color Code	Red
Trade Name	HYLINK™
Die Index	49
UPC	621945433700
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	621945433700
UPC 14 Digit GTIN	00621945433700

Logistics

Minimum Pack Quantity	12
Pallet Quantity	6000
Carton Quantity	25

Operational

Temperature Rating	194
--------------------	-----



A Hubbell brand