



YSA25R2N, Disconnectable Terminal with Slotted Pad

By Burndy
Catalog # [YSA25R2N](#)



DISCONNECTABLE TERMINAL(WITH SLOTTED PAD).

Features

- Disconnectable Terminal with Slotted Pad

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Size	1/0 AWG
Conductor - ACSR Str Size	1/0 (6/1) Raven AWG
Conductor - AL Str Size	1/0 AWG

Configuration

Connector Type	Terminal
----------------	----------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - B Length inch	1.64 in
Dimension - Outside Diameter inch	0.80 in

Dimension - Pad Width inch	1.90 in
Package Height	0.000 in
Dimension - Bolt Size fraction	1/2
Thickness - Pad	0.38 in
Dimension - Length Overall inch	6.25 in
Dimension - Thread Size	1/2

General

Die Index	• 659 • C
Trade Name	HYLUG™
Plated	N
Prefilled Oxide Inhibitor	Y
UPC 12 Digit	781810017081
UPC 14 Digit GTIN	00781810017081
Material	Aluminum
Plating Type	Unplated
UPC	781810017081

Logistics

Minimum Pack Quantity	4
Carton Quantity	8
Pallet Quantity	288

Product Assets

[Catalog \[English\]](#)