



YSA2R2N, Disconnectable Terminal with Slotted Pad

By Burndy
Catalog # [YSA2R2N](#)

DISCONNECTABLE TERMINAL(WITH SLOTTED PAD).



Features

- Disconnectable Terminal with Slotted Pad

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Size	2 AWG 1 AWG
Conductor - Copper Str Size Range	2 AWG - 1 AWG
Conductor - ACSR Str Size	2 (6/1) Sparrow AWG 2 (7/1) Sparate AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG
Conductor - AL Str Size	2 AWG 1 AWG
Conductor - AL Str Size Range	2 AWG - 1 AWG

Configuration

Connector Type	Terminal
----------------	----------

Dimensions

Package Length	0.000 in
Package Width	0.000 in

Package Weight	0.000 lb.
Dimension - B Length inch	1.62 in
Dimension - Outside Diameter inch	0.65 in
Dimension - Pad Width inch	1.90 in
Package Height	0.000 in
Dimension - Bolt Size fraction	1/2
Thickness - Pad	0.38 in
Dimension - Length Overall inch	6.17 in
Dimension - Thread Size	1/2

General

Die Index	243 - BG
Trade Name	HYLUG™
Plated	N
Prefilled Oxide Inhibitor	Y
UPC 12 Digit	781810017074
UPC 14 Digit GTIN	00781810017074
Material	Aluminum
Plating Type	Unplated
UPC	781810017074

Logistics

Minimum Pack Quantity	4
Carton Quantity	15
Pallet Quantity	540

Product Assets

[Catalog \[English\]](#)