



YSA321R2N, Disconnectable Terminal with Slotted Pad

By Burndy
Catalog # [YSA321R2N](#)



DISCONNECTABLE TERMINAL(WITH SLOTTED PAD).

Features

- Disconnectable Terminal with Slotted Pad

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Str Size	350 kcmil
Conductor - ACSR Str Size	• 300.0 (26/7) Ostrich kcmil • 336.4 (18/1) Merlin kcmil
Conductor - ACSR Str Size Range	300.0 (26/7) Ostrich kcmil-336.4 (18/1) Merlin kcmil
Conductor - AL Str Size	350 kcmil

Configuration

Connector Type	Terminal
----------------	----------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - B Length inch	3.06 in
Dimension - Outside Diameter inch	1.24 in

Dimension - L Length Overall mm	197 mm
Dimension - Pad Width inch	1.90 in
Package Height	0.000 in
Dimension - Bolt Size fraction	1/2
Thickness - Pad	0.38 in
Dimension - Length Overall inch	7.71 in
Dimension - Thread Size	1/2

General

Die Index	• 317 • M
Trade Name	HYLUG™
Plated	N
Prefilled Oxide Inhibitor	Y
UPC 12 Digit	781810017135
UPC 14 Digit GTIN	00781810017135
Material	Aluminum
Plating Type	Unplated
UPC	781810017135

Logistics

Minimum Pack Quantity	3
Carton Quantity	8
Pallet Quantity	2160

Product Assets

[Catalog \[English\]](#)