

YSCM133, Seamless Parallel Compression Splice Connector, 104,960-133,220 Circular Mils Cu

By Burndy
Catalog # [YSCM133](#)



104,960 - 133,220, Circular Mils, CU, SPLICE

Features

- Copper seamless barrel uninsulated parallel splice
- Designed to accommodate a wide range of stranded wires to be laid parallel inside the barrel and spliced together
- Electro-tin plated unless otherwise specified
- Barrel is color coded to ensure proper die and installation tooling is selected

Application

Wire Splice

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	Yes
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Range	104,960 - 133,220 Circular Mils
Conductor - Copper Str Size	• 1/0 • 2/0 AWG
Conductor Size	104,960-133,220 CMILS
Conductor Type	CODE
Conductor - Copper Str Size Range	1/0 -2/0 AWG

Configuration

Connector Type	Splice
----------------	--------

Current

Voltage Rating	35 kV
----------------	-------

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	21 mm
Dimension - Outside Diameter inch	0.64 in
Width	0.64 in
Dimension - Strip Length inch	1-1/16
Length	0.81 in
Height	0.64 in
Dimension - Length Overall inch	0.81 in
Dimensions	0.81 in x 0.64 in x 0.64 in

General

Trade Name	HYLINK™
Die Index	13
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Black
Sub Brand	HYLINK
UPC	781810358559
Type	YSCM
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810358559
UPC 14 Digit GTIN	00781810358559

Logistics

Minimum Pack Quantity	1
Pallet Quantity	69600
Carton Quantity	200

Product Assets

[Catalog \[English\]](#)