

YSCM212, Seamless Parallel Compression Splice Connector, 167,380-211,820 Circular Mils Cu

By Burndy
Catalog # [YSCM212](#)



167,380 - 211,820, Circular Mils, CU, SPLICE

Features

- Copper seamless barrel uninsulated parallel splice
- Designed to accommodate a wide range of stranded wires to be laid parallel inside the barrel and spliced together
- Electro-tin plated unless otherwise specified
- Barrel is color coded to ensure proper die and installation tooling is selected

Application

Wire Splice

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	Yes
EU RoHS Indicator	Yes
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - ETL	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Range	167,380 - 211,820 Circular Mils
Conductor - Copper Str Size	• 3/0 AWG • 4/0 AWG
Conductor Size	167,380-211,820 CMILS
Conductor Type	CODE
Conductor - Copper Str Size Range	3/0 AWG-4/0 AWG

Configuration

Connector Type	Splice
----------------	--------

Current

Voltage Rating	35 kV
----------------	-------

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	22 mm
Dimension - Outside Diameter inch	0.78 in
Width	0.78 in
Dimension - Strip Length inch	1-1/16
Length	0.88 in
Height	0.78 in
Dimension - Length Overall inch	0.88 in
Dimensions	0.88 in x 0.78 in x 0.78 in

General

Trade Name	HYLINK™
Die Index	15
Feature - Barrel Type	Standard
Feature - Barrel Style	Chamfered
Plated	Y
Color Code	Purple
Sub Brand	HYLINK
UPC	781810358573
Type	YSCM
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810358573
UPC 14 Digit GTIN	00781810358573

Logistics

Minimum Pack Quantity	1
Pallet Quantity	37000
Carton Quantity	200

Product Assets

[Catalog \[English\]](#)