



YSD25R2R, Aluminum Splice

By Burndy
Catalog # [YSD25R2R](#)

Al LINKIT Compression Splice, 1/0 AWG ACSR, 1/0 Str. Al/Cu, 2/0 AWG Al Compt(SideA), #2 AWG ACSR, #1 - #2 Str. Al/Cu, 1/0 AWG Al Compt(Side B)

Features

- Aluminum Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	1/0 AWG
Conductor - Copper Str Size B	1 AWG, 2 AWG
Conductor - AL Str Size A	1/0 AWG
Conductor - AL Str Size B	1 AWG, 2 AWG
Conductor - AL Str Size B	1 AWG-2 AWG
Range	
Conductor - ACSR Str Size A	1/0 AWG
Conductor - ACSR Str Size B	2/0 AWG
Conductor - Copper Str Size B	1 AWG- 2 AWG
Range	

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in



Dimension - L Length Overall	102 mm
mm	
Dimension - Outside Diameter	.3125 in
inch	
Dimension - Length Overall	4 in
inch	

General

Plated	N
Trade Name	LINKIT™
Die Index	249 840
UPC	781810195086
Color Code - Side B	Red
Color Code - Side A	Yellow
Type	Service Entrance, Uninsulated
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810195086
UPC 14 Digit GTIN	00781810195086

Logistics

Minimum Pack Quantity	25
Pallet Quantity	7400
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)