



YSD26R2R, Aluminum Sleeve with Solid Center Barrier

By Burndy
Catalog # [YSD26R2R](#)



Aluminum compression sleeve with solid center barrier, Designed for commercial and heavy residential services

Features

- Aluminum Compression Sleeve
- Solid Center Barrier

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	2/0 AWG
Conductor - Copper Str Size B	2 AWG, 3 AWG, 4 AWG
Conductor - AL Str Size A	2/0 AWG
Conductor - AL Str Size B	2 AWG, 3 AWG, 4 AWG
Conductor - AL Str Size B	2 AWG-4 AWG
Range	
Conductor - ACSR Str Size A	2/0 (6/1) Quail AWG
Conductor - ACSR Str Size B	4/0 AWG
Conductor - Copper Str Size B	2 AWG-4 Awg
Range	

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in
Dimension - L Length Overall	102 mm
Dimension - Outside Diameter	.3125 in
Dimension - Length Overall	4 in

General

Plated	N
Trade Name	LINKIT™
Die Index	249 - K-840
UPC	781810144008
Color Code - Side B	Red
Color Code - Side A	Gray
Type	Service Entrance, Uninsulated
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810144008
UPC 14 Digit GTIN	00781810144008

Logistics

Minimum Pack Quantity	1
Pallet Quantity	7400
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)