



YSD26R4W, Aluminum Splice

By Burndy
Catalog # [YSD26R4W](#)



Al LINKIT Splice, 2/0 AWG ACSR/Al/Cu, 3/0 Al Comp.(Side A),
#6 AWG ACSR/Al/Cu,#4 Al Comp.(Side B)

Features

- Aluminum Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	2/0 AWG
Conductor - Copper Str Size B	4 AWG, 5 AWG, 6 AWG
Conductor - AL Str Size A	2/0 AWG
Conductor - AL Str Size B	4 AWG, 5 AWG, 6 AWG
Conductor - AL Str Size B	4 AWG-6 AWG
Range	
Conductor - ACSR Str Size A	2/0 AWG
Conductor - ACSR Str Size B	6 AWG
Conductor - Copper Str Size B	4 AWG-6 AWG
Range	

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

Dimension - L Length Overall	102 mm
mm	
Dimension - Outside Diameter	.3125 in
inch	
Dimension - Length Overall	4 in
inch	

General

Plated	Y
Trade Name	LINKIT™
Die Index	249 840
UPC	781810182840
Color Code - Side B	Blue
Color Code - Side A	Gray
Type	Service Entrance, Uninsulated
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810182840
UPC 14 Digit GTIN	00781810182840

Logistics

Minimum Pack Quantity	50
Pallet Quantity	7400
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)