



YSD27R2R, Aluminum Sleeve with Solid Center Barrier

By Burndy
Catalog # [YSD27R2R](#)



AL compression sleeve with solid center barrier, Designed for commercial and heavy residential services, Color Code: Black (Side A), Red (Side B)

Features

- Aluminum Compression Sleeve
- Solid Center Barrier

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	3/0 AWG
Conductor - Copper Str Size B	1 AWG, 2 AWG
Conductor - AL Str Size A	3/0 AWG
Conductor - AL Str Size B	1 AWG, 2 AWG
Conductor - AL Str Size B	1 AWG-2 AWG
Range	
Conductor - ACSR Str Size A	3/0 (6/1) Pigeon AWG
Conductor - ACSR Str Size B	• 2 (6/1) Sparrow AWG • 2 (7/1) Sparate AWG
Conductor - Copper Str Size B	1 AWG-2 AWG
Range	
Conductor - ACSR Str Size B	2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG
Range	

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	102 mm
Dimension - Outside Diameter	.3125 inch
Dimension - Length Overall	4 inch

General

Plated	N
Trade Name	LINKIT™
Die Index	• 249 • K-840
UPC	781810145005
Color Code - Side B	Red
Color Code - Side A	Black
Type	Service Entrance, Uninsulated
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810145005
UPC 14 Digit GTIN	00781810145005

Logistics

Minimum Pack Quantity	1
Pallet Quantity	7400
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)