



YSD28R25RBOX100, Aluminum LINKIT Splice, 100 piece box

By Burndy
Catalog # [YSD28R25RBOX100](#)

Al LINKIT Splice Box, 4/0 AWG ACSR/Al/Cu, 300 kcmil Al Comp.
(Side A), 1/0 AWG ACSR/Al/Cu, 2/0 AWG Al Comp.(Side B)

Features

- Aluminum Compression Sleeve
- Solid Center Barrier

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	4/0 AWG
Conductor - Copper Str Size B	1/0 AWG
Conductor - AL Str Size A	4/0 AWG
Conductor - AL Str Size B	1/0 AWG
Conductor - ACSR Str Size A	4/0 AWG
Conductor - ACSR Str Size B	1/0 Awg

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	102 mm
mm	



Dimension - Outside Diameter	.3125 in
inch	
Dimension - Length Overall	4 in
inch	

General

Plated	N
Trade Name	LINKIT™
Die Index	• 249 • 840
UPC	781810047064
Color Code - Side B	Yellow
Color Code - Side A	Pink
Type	Service Entrance, Uninsulated
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810047064
UPC 14 Digit GTIN	00781810047064

Logistics

Minimum Pack Quantity	1
Pallet Quantity	9000
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)



A Hubbell brand