



YSD28R2W, Aluminum Sleeve with Solid Center Barrier

By Burndy
Catalog # [YSD28R2W](#)

AL compression sleeve with solid center barrier, Designed for commercial and heavy residential services, Color Code: Pink (Side A), Orange (Side B)

Features

- Aluminum Compression Sleeve
- Solid Center Barrier

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	4/0 AWG
Conductor - Copper Str Size B	• 4 AWG • 3 AWG • 2 AWG
Conductor - AL Str Size A	4/0 AWG
Conductor - AL Str Size B	• 4 AWG • 3 AWG • 2 AWG
Conductor - AL Str Size B Range	4 AWG-2 AWG
Conductor - ACSR Str Size A	4/0 (6/1) Penguin AWG
Conductor - ACSR Str Size B	• 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG
Conductor - Copper Str Size B Range	4 AWG-2 AWG
Conductor - ACSR Str Size B Range	4 (6/1) Swan AWG-4 (7/1) Swanate AWG

Dimensions



Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	102 mm
Dimension - Outside Diameter	.3125 in
Dimension - Length Overall	4 in

General

Plated	Y
Trade Name	LINKIT™
Die Index	• 249 • K-840
UPC	781810146057
Color Code - Side B	Orange
Color Code - Side A	Pink
Type	Service Entrance, Uninsulated
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810146057
UPC 14 Digit GTIN	00781810146057

Logistics

Minimum Pack Quantity	25
Pallet Quantity	7400
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)