



YSD2R2R, Aluminum LINKIT Splice

By Burndy
Catalog # [YSD2R2R](#)

Al LINKIT Compression Splice, #2 AWG ACSR, #1 - #2 Str. Al/Cu, 1/0 AWG Al Compt(Side A & B)



Features

- Aluminum Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	1 AWG, 2 AWG
Conductor - Copper Str Size B	1 AWG, 2 AWG
Conductor - Copper Str Size A Range	1 AWG-2 AWG
Conductor - AL Str Size A	1 AWG, 2 AWG
Conductor - AL Str Size B	1 AWG, 2 AWG
Conductor - AL Str Size A Range	1 AWG-2 AWG
Conductor - AL Str Size B Range	1 AWG-2 AWG
Conductor - ACSR Str Size A	2 (6-1) AWG, 2(7-1) Awg
Conductor - ACSR Str Size B	2 (6-1) AWG, 2(7-1) Awg
Conductor - ACSR Str Size A Range	2 (6-1) AWG- 2(7-1) Awg
Conductor - Copper Str Size B Range	1 AWG-2 AWG
Conductor - ACSR Str Size B Range	2 (6-1) AWG- 2(7-1) Awg

Dimensions

Dimension - L Length Overall	102 mm
Dimension - Outside Diameter	.3125 inch
Dimension - Length Overall	4 in

General

Plated	N
Trade Name	LINKIT™
Die Index	249 840
UPC	781810111185
Color Code - Side B	Red
Color Code - Side A	Red
Type	Service Entrance, Uninsulated
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810111185
UPC 14 Digit GTIN	00781810111185

Logistics

Minimum Pack Quantity	25
Pallet Quantity	7400
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)