




YSE14H, Nylon Splice, 16 - 14 AWG, Inspection Window

By Burndy
Catalog # [YSE14H](#)



Nylon Splice, 16-14 AWG, Tin Plated, Seamless Copper Tubing, Integral Barrel/Insulation Grip, Bulk Package

Features

- Manufactured from tin plated, seamless electrolytic copper tubing with integral barrel/insulation grip - providing maximum conductivity and tensile strength along with excellent cable support and strain relief
- Split heavy wall insulation grip for stronger insulation grip and strain relief
- Smooth funnel entry for easy wire insertion
- Transparent nylon insulation for easy wire insertion

Application

For Splicing Aircraft And Commercial Flexible Cables

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL486
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	• 16 • 14
Conductor Size	16 - 14 AWG
Conductor - Copper Str Aircraft Size Range	AN 16-AN 14
Conductor - Copper Str Aircraft Size	• AN 16 • AN 14
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	16-14

Configuration

Connector Type	Seamless Butt Splice
----------------	----------------------

Current

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Outside Diameter inch	0.15 in
Dimension - Strip Length inch	11/32
Dimension - B Length fraction	3/13 in
Dimension - B Length inch	0.23 in
Dimension - Diameter Max Size inch	0.15 in
Dimension - Length Overall inch	1.36 in

General

Product Family	COMPRESSION
Insulation Type	Nylon
Trade Name	INSULINK™
Insulation	Y
Plated	Yes
Color Code	Blue
Sub Brand	INSULINK
Product Type	Splice
UPC	781810803868
Type	YSE-H
Construction Material - Main Material	Copper
Plating Type	Tin
UPC 12 Digit	781810803868
UPC 14 Digit GTIN	00781810803868

Logistics

Minimum Pack Quantity	1000
Pallet Quantity	99999
Carton Quantity	1000

Operational

Temperature Rating	105
--------------------	-----

Product Assets

[Catalog \[English\]](#)