



YSE18HBOX, Nylon Splice, 22 - 18 AWG, Inspection Window

By Burndy

Catalog # [YSE18HBOX](#)

Nylon Splice, 22-18 AWG, Tin Plated, Seamless Copper Tubing, Integral
Barrel/Insulation Grip



Features

- Manufactured from tin plated, seamless electrolytic copper tubing with integral barrel/insulation grip - providing maximum conductivity and tensile strength along with excellent cable support and strain relief
- Split heavy wall insulation grip for stronger insulation grip and strain relief
- Smooth funnel entry for easy wire insertion
- Transparent nylon insulation for easy wire insertion

Application

For Splicing Aircraft And Commercial Flexible Cables

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL486
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	• 20 • 18
Conductor Size	22 - 18 AWG
Conductor - Copper Solid Size	• 20 • 18
Conductor - Copper Str Aircraft Size Range	AN 22-AN 18
Conductor - Copper Str Aircraft Size	• AN 22 • AN 20 • AN 18
Conductor - Copper Solid Size Range	20-18
Conductor Type	CU C Str-Size
Conductor - Copper Str Size Range	20-18

Configuration

Connector Type	Seamless Butt Splice
----------------	----------------------

Current



A Hubbell brand

Voltage - Maximum	600 V
-------------------	-------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	31 mm
Dimension - Outside Diameter inch	0.12 in
Dimension - Strip Length inch	9/32 in
Dimension - B Length fraction	2/9 in
Dimension - B Length inch	0.22 in
Dimension - Diameter Max Size inch	0.12 in
Dimension - Length Overall inch	1.22 in
Cable Insulation Diameter Maximum	0.115 in

General

Product Family	COMPRESSION
Insulation Type	Nylon
Trade Name	INSULINK™
Insulation	Y
Plated	Yes
Color Code	Red
Sub Brand	INSULINK
Product Type	Splice
UPC	781810566602
Type	YSE-H
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810566602
UPC 14 Digit GTIN	00781810566602

Logistics

Minimum Pack Quantity	100
Pallet Quantity	99999
Carton Quantity	1200

Operational

Temperature Rating	105
--------------------	-----

Product Assets

[Catalog \[English\]](#)