



YSH3939 Compression H-Tap Connector

By Burndy
Catalog # YSH3939

Copper Split Compression Wye Tap Connector, 750-350 (550-500) (Tap),
Provides maximum design and installation flexibility

Features

- Accommodates a wide range of Run/Tap Copper cable combinations including both flexible and code combinations allowing maximum flexibility
- Tap grooves function independently from each other, use of one tap is required, balance may be used or left empty

Application

For High Voltage (15 KV) Power Cables With Copper Conductors

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	500-750 kcmil
Conductor - Copper Str Run	• 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil
Conductor - Copper Str Tap Range	350 kcmil-750 kcmil
Conductor - Copper Str Tap	• 350 kcmil • 400 kcmil • 450 kcmil • 500 kcmil • 550 kcmil • 600 kcmil • 700 kcmil • 750 kcmil

Configuration

Connector Type	H-Tap
----------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	75.4 mm
Dimension - Height inch	2.97 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Strip Length inch	1 1/2
Dimension - Width mm	38 mm
Dimension - Width inch	1.50 in
Dimension - Length Overall inch	3.00 in

General

Trade Name	CRIMPIT™
Die Index	KR
Plated	Yes
Color Code	Yellow
Sub Brand	CRIMPIT
Product Type	Compression
UPC	781810036983
Type	Taps
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810036983
UPC 14 Digit GTIN	00781810036983

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1200
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)