



YSH4429 Compression H-Tap Connector

By Burndy
Catalog # [YSH4429](#)

Cu Compression Split Y-Splice, 1000 Kcmil (Run), 250 Kcmil (Tap)

Features

- Accommodates a wide range of Run/Tap Copper cable combinations including both flexible and code combinations allowing maximum flexibility
- Tap grooves function independently from each other, use of one tap is required, balance may be used or left empty

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Configuration

Connector Type	H-Tap
----------------	-------

Dimensions

Package Height	0.000 in
----------------	----------

Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Plated	Y
UPC	781810196854
Type	Taps
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810196854
UPC 14 Digit GTIN	00781810196854

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1440
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)