



YSH4444 Compression H-Tap Connector

By Burndy
Catalog # [YSH4444](#)

Cu Compression Split Y-Splice, Accom: Main- 1000- 750 CODE, 777-500 Flex, 777-750 Flex, Tap- 1000-750 Code, 777- 500 Flex, 350 Flex

Features

- Accommodates a wide range of Run/Tap Copper cable combinations including both flexible and code combinations allowing maximum flexibility
- Tap grooves function independently from each other, use of one tap is required, balance may be used or left empty

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Run Range	1000- 750 CODE, 777-500 Flex, 777-750 Flex,
Conductor - Copper Str Run	1000- 750 CODE, 777-500 Flex, 777-750 Flex,
Conductor - Copper Str Tap Range	1000-750 Code, 777- 500 Flex, 350 Flex
Conductor - Copper Str Tap	1000-750 Code, 777- 500 Flex, 350 Flex

Configuration

Connector Type	H-Tap
----------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Length	2.5 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Height	3.38 in
Width	1.7 in
Dimensions	2.5 in x 1.7 in x 3.38 in

General

Plated	Y
Color Code	White
Trade Name	CRIMPIT™
Die Index	1102
UPC	781810303245
Type	Taps
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810303245
UPC 14 Digit GTIN	00781810303245

Logistics

Minimum Pack Quantity	1
Pallet Quantity	960
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)