


YSHG3434 Compression H-Tap Connector

By Burndy
Catalog # [YSHG3434](#)

Copper Compression Double H- Tap Connector, 4/0 AWG - 400 kcmil (Tap), # 6 Rebar/ 3/4" Ground Rod/ 400 to 250 kcmil Cu Cable



Features

- UL467 Listed
- Suitable for direct burial in earth or concrete
- High conductivity copper extrusion minimizes resistance and eliminates corrosion due to dissimilar metals
- Grooves are prefilled with PENETROX™ E2 oxide inhibitor and individually sealed inhibiting moisture and contaminants

Application

For Direct Burial In Earth Or Concrete

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
Industry Standard(s)	UL 467, Direct Burial
Certification - ETL	No
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	Yes
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Rebar Run Range	6
Conductor - Rebar Run	6
Conductor - Rod Run Range	3/4 in
Conductor - Rod Run	3/4 in
Conductor - Copper Str Run Range	250 kcmil-400 kcmil
Conductor - Copper Str Run	• 250 kcmil • 300 kcmil • 350 kcmil • 400 kcmil
Conductor - Copper Str Tap Range	4/0 AWG-400 kcmil
Conductor - Copper Str Tap	• 4/0 AWG • 250 kcmil • 300 kcmil

- 350 kcmil
- 400 kcmil

Configuration

Physical Attribute - Number of Crimps Required	4
Connector Type	H-Tap

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Width mm	62 mm
Dimension - Width inch	2.43 in
Dimension - Length Overall inch	2.44 in

General

Trade Name	HYGROUND®
Die Index	1104
Plated	No
Sub Brand	CRIMPIT
Product Type	Compression
UPC	781810129692
Type	Taps
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810129692
UPC 14 Digit GTIN	00781810129692

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2400
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)