



YSHG3939 Compression H-Tap Connector

By Burndy
Catalog # [YSHG3939](#)

Copper Compression Double H- Tap Connector,1" Ground Rod or 500 kcmil (Run), 500 -350 kcmil (Tap)

Features

- UL467 Listed
- Suitable for direct burial in earth or concrete
- High conductivity copper extrusion minimizes resistance and eliminates corrosion due to dissimilar metals
- Grooves are prefilled with PENETROX™ E2 oxide inhibitor and individually sealed inhibiting moisture and contaminants

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Certification - UL Listed Direct	Yes
Burial	
Industry Standard(s)	UL 467, Direct Burial
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Rod Run Range	1" Ground rod
Conductor - Copper Str Run Range	500 kcmil
Conductor - Copper Str Tap Range	500-350 kcmil

Configuration

Physical Attribute - Number of	2
Crimps Required	
Connector Type	H-Tap

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Plated	N
Trade Name	HYGROUND®
Die Index	KR
UPC	781810129562
Type	Taps
Material	Copper
Plating Type	Unplated
UPC 12 Digit	781810129562
UPC 14 Digit GTIN	00781810129562

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1440
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)