



YSHG4429TNCompression H-Tap Connector

By Burndy
Catalog # YSHG4429TN

Tin plated Copper Compression Double H- Tap Connector, 2
AWG - 250 kcmil (Tap), #8 & #9 Rebar/ 1" Ground Rod

Features

- UL467 Listed
- Suitable for direct burial in earth or concrete
- High conductivity copper extrusion minimizes resistance and eliminates corrosion due to dissimilar metals
- Grooves are prefilled with PENETROX™ E2 oxide inhibitor and individually sealed inhibiting moisture and contaminants

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards	UL467
Met	
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Certification - UL Listed Direct	Yes
Burial	
Industry Standard(s)	UL 467, Direct Burial
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Tap	2 AWG-250 kcmil
Range	
Conductor - Copper Str Tap	• 2 AWG • 1 AWG • 1/0 AWG • 2/0 AWG • 3/0 AWG • 4/0 AWG

- 250 kcmil

Configuration

Connector Type	H-Tap
----------------	-------

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in

General

Plated	Y
Trade Name	HYGROUND®
Die Index	KR
UPC	781810327326
Type	Taps
Material	Copper
Plating Type	Tin - Electro Plated
UPC 12 Digit	781810327326
UPC 14 Digit GTIN	00781810327326

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2880
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)



A Hubbell brand