



YSM44L131, Parallel Splice 1.2" ID 1.31" Length

By Burndy
Catalog # [YSM44L131](#)

Uninsulated Parallel Splice For 1000 kcmil



Features

- Seamless tubing
- Beveled barrel for ease of wire entry
- Tin plated
- Parallel design results in only one crimp necessary
- Uninsulated barrel provides an economical termination solution when insulation is not specified

Specifications

Certification - cULus	N
Certification - UL Recognized	N
Certification - ETL	No
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Solid Size Range	N/A
Conductor - Copper Str Compact Size	1000 kcmil
Conductor - Copper Str Compact Size Range	1000 kcmil
Conductor - Copper Str Size	1000 kcmil
Conductor - Copper Str Size Range	1000 kcmil
Conductor Type	• CU C Solid-Size • CU C Str-Size

Configuration

Connector Type	Parallel Splice
----------------	-----------------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Package Weight	0.000 lb.
Dimension - B Length inch	1.15 in
Dimension - Outside Diameter inch	1.50 in
Package Height	0.000 in
Length	1.352 in
Dimension - Inside Diameter inch	1.15 in
Dimension - Length Overall inch	1.35 in
Dimension - Thread Size	-

General

Trade Name	N
Plated	Y
Feature - Barrel Style	Chamfered
Insulation	N
UPC 12 Digit	781810371152
UPC 14 Digit GTIN	00781810371152
Material	Copper
Plating Type	Tin
UPC	781810371152

Logistics

Minimum Pack Quantity	1
Carton Quantity	50
Pallet Quantity	7400

Product Assets

[Catalog \[English\]](#)