



YSM6C, Uninsulated Parallel Splice For 10,380 - 26,813 cmils

By Burndy
Catalog # [YSM6C](#)

Uninsulated Parallel Splice For 10,380 - 26,813 cmils, Seamless Tubing, Beveled Barrel, Tin Plated

Features

- Seamless tubing
- Beveled barrel for ease of wire entry
- Tin plated
- Parallel design results in only one crimp necessary
- Uninsulated barrel provides an economical termination solution when insulation is not specified

Application

HYLINK Type YSM seamless parallel splice connector permits wires to be laid parallel inside the connector and spliced together with the BURNDY family of HYTOOL installation tooling

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	No
Certification - cULus	No
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	10,380 - 26,813 cmils
Conductor - Copper Solid Size	• 14 AWG • 13 AWG • 12 AWG
Conductor - Copper Solid Size Range	14 AWG-12 AWG
Conductor Type	• CU C Solid-Size • CU C Str-Size
Conductor - Copper Str Size Range	14 AWG-12 AWG
Conductor - Copper Str Size	• 14 AWG

- 12 AWG

Configuration

Connector Type	Parallel Splice
----------------	-----------------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - Outside Diameter inch	0.31 in
Dimension - Length Overall inch	0.44 in
Dimension - Strip Length inch	1/2

General

Feature - Barrel Style	Chamfered
Plated	Yes
Product Family	COMPRESSION
Trade Name	HYLINK™
Sub Brand	HYLINK
Product Type	Splice
UPC	781810805787
Type	YSM
Material	Copper
Plating Type	Tin
UPC 12 Digit	781810805787
UPC 14 Digit GTIN	00781810805787

Logistics

Minimum Pack Quantity	200
Carton Quantity	200

Operational

Temperature Rating	90
--------------------	----

Product Assets

[Catalog \[English\]](#)