



YSMA1C4SL, Aluminum Seamless Compression Splice, permits parallel wire or single wire splice with 1 or more taps

By Burndy
Catalog # [YSMA1C4SL](#)

Seamless Splice Connector

Features

- Uninsulated aluminum compression connector
- The connection is irreversible and maintenance free
- cULus Listed Wire Connector File #E9498
- Rated for aluminum or copper 900C and up to 35kV
- Connectors are tin plated
- Connectors are clearly marked with the wire size range, the name BURNDY, catalog number and cULus logo
- Connectors are crimped once with our dieless 444S or 644 series of installation tools
- cULus Listed Wire Connector using the BURNDY® Engineered System
- Add suffix -WC to the catalog number (YSMA1C4SLWC) and the connector will be kitted with a heavy wall heat shrink end cap

Conductor

Conductor Size	6 AWG-1/0 AWG
Conductor - AL Str Size Range	6 AWG - 1/0 AWG
Wire Length	0.98 in
Conductor Type	CODE
Conductor - Copper Str Size Range	6 AWG - 1/0 AWG
Conductor - Material	ALUMINUM / COPPER



Wire Size6 AWG-1/0 AWG

Configuration

Connector TypeDUAL RATED

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Outside Diameter	1.13 in
Package Width	0.000 in
Dimension - Length Overall	1.23 in

General

UPC	621945643659
Material	ALUMINUM

Logistics

Pallet Quantity	22500
Carton Quantity	250

Product Assets

[Catalog \[English\]](#)