



YSR10CFX12CLTCKITC, Compression Splice Reducer, Barrel, A #14-10 AWG, Barrel B #14-10 AWG, includes clear heat shrink

By Burndy
Catalog # YSR10CFX12CLTCKITC

CU Splice Reducer, Barrel A 14-10 AWG, Barrel B 14-10 AWG, Standard Barrel, Internal Chamfer, Tin Plated, Connector is UL/CSA, 90°C Up to 35kV, Kit comes with Clear Heat Shrink.

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	10 AWG-12 AWG
Conductor - Copper Flex K Size B Range	#14-#10 AWG
Conductor - Copper Flex K Size A Range	#14-#10 AWG
Conductor - Copper Flex M Size A Range	#14-#10 AWG
Conductor - Copper Flex M Size B Range	#14-#10 AWG
Conductor - Copper Str Size	10 AWG-12 AWG
Conductor - Copper Flex I Size B Range	#14-#10 AWG
Conductor - Copper Flex G Size A Range	#14-#10 AWG
Conductor Size	10 AWG-12 AWG
Conductor - Copper Str Size B	10 AWG



Conductor - Copper Str Size A Range	#14-#10 AWG
Conductor - Copper Flex G Size B Range	#14-#10 AWG
Conductor - Copper Str Run A	10 AWG
Conductor - Copper Solid Size A	• 12 • 11 • 10
Conductor - Copper Solid Size B	• 12 • 11 • 10
Conductor Type	CODE/FLEX
Conductor - Copper Str Size B Range	10 AWG
Conductor - Copper Flex H Size A Range	#14-#10 AWG
Conductor - Copper Flex H Size B Range	#14-#10 AWG
Conductor - Copper Flex I Size A Range	#14-#10 AWG

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	37 mm
Dimension - Strip Length inch	0.63 in
Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.66 in
Dimension - Length BB inch	0.66 in
Dimension - Length Overall inch	1.45 in

General

Trade Name	HYREDUCER™
Feature - Barrel Type	Standard
Feature - Barrel Style	Skived
Plated	Y
UPC	781810473993
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810473993
UPC 14 Digit GTIN	00781810473993

Logistics

Minimum Pack Quantity	1
Pallet Quantity	6000
Carton Quantity	25

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[French, English\]](#)



A Hubbell brand