



YSR26FX2CFXLTKITC, Cu Splice Reducer with Clear Heat Shrink, Barrel A: 2/0 Flex/AWG, Barrel B: 2 Flex/AWG

By Burndy
Catalog # [YSR26FX2CFXLTKITC](#)

CU Splice Reducer, Barrel A 2/0 Flex G,H,I,K,M,DLO, 2/0 AWG, Barrel B 2 Flex G,H,I,K,M,DLO, 2 AWG CU, Kit includes clear heat shrink

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	2/0 AWG-2 AWG
Conductor - Copper Flex K Tap	2 AWG
Conductor - Copper Flex K Size A	2/0 AWG
Conductor - Copper Flex K Size B	2 AWG
Conductor - Copper Flex M Size B	2 AWG
Conductor - Copper Flex M Run	2/0 AWG
Conductor - Copper Flex M Size A	2/0 AWG
Conductor - Copper Str Size	2/0 AWG-2 AWG
Conductor - Copper Flex I Tap	2 AWG
Conductor - Copper Flex K Run	2/0 AWG



Conductor - Copper Flex I Size B	2 AWG
Conductor - Copper Flex G Size A	2/0 AWG
Conductor - Copper Flex G Size B	2 AWG
Conductor - Copper Flex G Run	2/0 AWG
Conductor - Copper Str Size A	2/0 AWG
Conductor - Copper Flex H Run	2/0 AWG
Conductor Size	2/0 AWG-2 AWG
Conductor - Copper Str Size B	2 AWG
Conductor - Copper Flex H Size A	2/0 AWG
Conductor - Copper Flex G Tap	2 AWG
Conductor - Copper Flex M Tap	2 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	2 AWG
Conductor - Copper Flex I Run	2/0 AWG
Conductor - Copper Flex H Size B	2 AWG
Conductor - Copper Str Size B Range	2 AWG
Conductor - Copper Flex I Size A	2/0 AWG

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	61 mm
Dimension - Strip Length inch	1.10 in
Dimension - B Length fraction	1-3/16 in
Dimension - B Length inch	1.16 in
Dimension - Length BB inch	0.82 in

Dimension - Length Overall inch	2.48 in	Color Code - Side A Type	Black YSR-TC
		Construction Material - Main Material	Copper Copper
General		Plating Type	Tin - Electro Plated
Trade Name	HYREDUCER™	Finish Type	Tin-Plated
Die Index	13/10	UPC 12 Digit	781810362600
Die Index - Element A	13	UPC 14 Digit GTIN	00781810362600
Die Index - Element B	10		
Die Index Run Side	13		
Die Index Tap Side	10		
Feature - Barrel Type	Standard	Logistics	
Feature - Barrel Style	Skived	Minimum Pack Quantity	1
Plated	Y	Pallet Quantity	2880
Color Code	Black, Brown	Carton Quantity	12
Sub Brand	HYREDUCER		
UPC	781810362600	Product Assets	
Color Code - Side B	Brown	Catalog [English]	
		Installation Manual [French, English]	



A Hubbell brand