



YSR282CFXLTKITC, Cu Splice Reducer with Clear Heat Shrink, Barrel A: 4/0 AWG, Barrel B: 2 Flex/AWG

By Burndy
Catalog # YSR282CFXLTKITC

CU Splice Reducer, Barrel A 4/0 AWG, Barrel B 2 Flex
G,H,I,K,M,DLO, 2 AWG CU, Kit includes clear heat shrink

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	4/0 AWG-2 AWG
Conductor - Copper Flex K Tap	2 AWG
Conductor - Copper Flex K Size B	2 AWG
Conductor - Copper Flex M Size B	2 AWG
Conductor - Copper Str Size	4/0 AWG-2 AWG
Conductor - Copper Flex I Tap	2 AWG
Conductor - Copper Flex I Size B	2 AWG
Conductor - Copper Flex G Size B	2 AWG
Conductor - Copper Str Size A	4/0 AWG
Conductor Size	4/0 AWG-2 AWG
Conductor - Copper Flex G Tap	2 AWG
Conductor - Copper Flex M Tap	2 AWG



Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	2 AWG
Conductor - Copper Flex H Size B	2 AWG

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	69 mm
Dimension - Strip Length inch	1.24 in
Dimension - B Length fraction	1-5/16 in
Dimension - B Length inch	1.30 in
Dimension - Length BB inch	0.82 in
Dimension - Length Overall inch	2.70 in

General

Trade Name	HYREDUCER™
Die Index	15/10
Die Index - Element A	15
Die Index - Element B	10
Die Index Run Side	15
Die Index Tap Side	10
Feature - Barrel Type	Standard
Feature - Barrel Style	Skived
Plated	Y
Color Code	Purple, Brown
Sub Brand	HYREDUCER
UPC	781810345566
Color Code - Side B	Brown
Color Code - Side A	Purple
Type	YSR-TC
Construction Material - Main Material	Copper

Plating Type	Tin - Electro Plated	Pallet Quantity	2880
Finish Type	Tin-Plated	Carton Quantity	12
UPC 12 Digit	781810345566	Product Assets	
UPC 14 Digit GTIN	00781810345566		
Logistics		Catalog [English]	
		Installation Manual [French, English]	

Minimum Pack Quantity	1
-----------------------	---

