



YSR284CFXLTKITC, Compression Splice Reducer, Barrel A 4/0 AWG, Barrel B #4 AWG, includes clear heat shrink

By Burndy
Catalog # YSR284CFXLTKITC

CU Splice Reducer, Barrel A 4/0 AWG, Barrel B 4 Flex
G,H,I,K,M,DLO, 4 AWG CU, Kit includes clear heat shrink

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	4/0 AWG-4 AWG
Conductor - Copper Flex K Tap	4 AWG
Conductor - Copper Flex K Size	4 AWG
B	
Conductor - Copper Flex M Size	4 AWG
B	
Conductor - Copper Str Size	4/0 AWG-4 AWG
Conductor - Copper Flex I Tap	4 AWG
Conductor - Copper Flex I Size	4 AWG
B	
Conductor - Copper Flex G Size	4 AWG
B	
Conductor Size	4/0 AWG-4 AWG
Conductor - Copper Flex G Tap	4 AWG
Conductor - Copper Flex M Tap	4 AWG
Conductor Type	CODE/FLEX



Conductor - Copper Flex H Tap	4 AWG
Conductor - Copper Flex H Size	4 AWG
B	

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	68 mm
mm	
Dimension - Strip Length inch	1.24 in
Dimension - B Length fraction	1-5/16 in
Dimension - B Length inch	1.30 in
Dimension - Length BB inch	0.74 in
Dimension - Length Overall	2.69 in
inch	

General

Trade Name	HYREDUCER™
Die Index	15/8
Die Index - Element A	15
Die Index - Element B	8
Die Index Run Side	15
Die Index Tap Side	8
Feature - Barrel Type	Standard
Feature - Barrel Style	Skived
Plated	Y
Color Code	Purple, Gray
Sub Brand	HYREDUCER
UPC	781810490655
Color Code - Side B	Gray
Color Code - Side A	Purple
Type	YSR-TC
Construction Material - Main	Copper
Material	Copper
Plating Type	Tin - Electro Plated

Finish Type	Tin-Plated	Pallet Quantity	1728
UPC 12 Digit	781810490655	Carton Quantity	12
UPC 14 Digit GTIN	00781810490655		

Logistics

Minimum Pack Quantity1



A Hubbell brand

Product Assets

- Catalog [English]
- Installation Manual [French, English]