



YSR286CFXLTKITC, Compression Splice Reducer, Barrel A 4/0 AWG, Barrel B #6 Flex, includes clear heat shrink

By Burndy
Catalog # YSR286CFXLTKITC

CU Splice Reducer, Barrel A 4/0 AWG, Barrel B 6 Flex
G,H,I,K,M,DLO, 6 AWG CU, Kit includes clear heat shrink

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	4/0 AWG-6 AWG
Conductor - Copper Flex K Tap	6 AWG
Conductor - Copper Flex K Size B	6 AWG
Conductor - Copper Flex M Size B	6 AWG
Conductor - Copper Str Size	4/0 AWG-6 AWG
Conductor - Copper Flex I Tap	6 AWG
Conductor - Copper Flex I Size B	6 AWG
Conductor - Copper Flex G Size B	6 AWG
Conductor - Copper Str Size A	4/0 AWG
Conductor Size	4/0 AWG-6 AWG
Conductor - Copper Flex G Tap	6 AWG
Conductor - Copper Flex M Tap	6 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	6 AWG



Conductor - Copper Flex H Size B
6 AWG

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	76 mm
Dimension - Strip Length inch	1.24 in
Dimension - B Length fraction	1-5/16 in
Dimension - B Length inch	1.30 in
Dimension - Length BB inch	0.73 in
Dimension - Length Overall inch	2.99 in

General

Trade Name	HYREDUCER™
Die Index	15/7
Die Index - Element A	15
Die Index - Element B	7
Die Index Run Side	15
Die Index Tap Side	7
Feature - Barrel Type	Standard
Feature - Barrel Style	Skived
Plated	Y
Color Code	Purple, Blue
UPC	781810345603
Color Code - Side B	Blue
Color Code - Side A	Purple
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810345603
UPC 14 Digit GTIN	00781810345603

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1728
Carton Quantity	12



A Hubbell brand

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[French, English\]](#)