



YSR28FX26FXLTCKITC, Compression Splice Reducer, Barrel A 4/0 Flex, Barrel B 2/0 Flex, includes clear heat shrink

By Burndy
Catalog # [YSR28FX26FXLTCKITC](#)

CU Splice Reducer, Barrel A 4/0 Flex G,H,I,K,M,DLO, 4/0 AWG, Barrel B 2/0 Flex G,H,I,K,M,DLO, 2/0 AWG CU, Kit includes clear heat shrink

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	4/0 AWG-2/0 AWG
Conductor - Copper Flex K Tap	2/0 AWG
Conductor - Copper Flex K Size A	4/0 AWG
Conductor - Copper Flex K Size B	2/0 AWG
Conductor - Copper Flex M Size B	2/0 AWG
Conductor - Copper Flex M Run	4/0 AWG
Conductor - Copper Flex M Size A	4/0 AWG
Conductor - Copper Str Size	4/0 AWG-2/0 AWG
Conductor - Copper Flex I Tap	2/0 AWG
Conductor - Copper Flex K Run	4/0 AWG



Conductor - Copper Flex I Size B	2/0 AWG
Conductor - Copper Flex G Size A	4/0 AWG
Conductor - Copper Flex G Size B	2/0 AWG
Conductor - Copper Flex G Run	4/0 AWG
Conductor - Copper Flex H Run	4/0 AWG
Conductor Size	4/0 AWG-2/0 AWG
Conductor - Copper Flex H Size A	4/0 AWG
Conductor - Copper Flex G Tap	2/0 AWG
Conductor - Copper Flex M Tap	2/0 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	2/0 AWG
Conductor - Copper Flex I Run	4/0 AWG
Conductor - Copper Flex H Size B	2/0 AWG
Conductor - Copper Flex I Size A	4/0 AWG

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	75 mm
Dimension - Strip Length inch	1.36 in
Dimension - B Length fraction	1-7/16 in
Dimension - B Length inch	1.43 in
Dimension - Length BB inch	1.13 in
Dimension - Length Overall inch	2.94 in

General

Trade Name	HYREDUCER™	Construction Material - Main	Copper
Die Index	15/13	Material	Copper
Die Index - Element A	15	Plating Type	Tin - Electro Plated
Die Index - Element B	13	Finish Type	Tin-Plated
Die Index Run Side	15	UPC 12 Digit	781810434376
Die Index Tap Side	13	UPC 14 Digit GTIN	00781810434376
Feature - Barrel Type	Standard	Logistics	
Feature - Barrel Style	Skived	Minimum Pack Quantity	12
Plated	Y	Pallet Quantity	1080
Color Code	Purple, Black	Carton Quantity	12
Sub Brand	HYREDUCER	Product Assets	
UPC	781810434376	Catalog [English]	
Color Code - Side B	Black	Installation Manual [French, English]	
Color Code - Side A	Purple		
Type	YSR-TC		

