



YSR29FX28LTCKITC, Compression Splice Reducer, Barrel A 250 kcmil, Barrel B 4/0 AWG, includes clear heat shrink

By Burndy

Catalog # [YSR29FX28LTCKITC](#)

CU Splice Reducer, Barrel A 250 kcmil, 4/0 G,H,I,K,M,DLO, Barrel B 4/0 AWG CU, Kit includes clear heat shrink

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Flex G Run	4/0 AWG
Conductor - Copper Flex H Run	4/0 AWG
Conductor Size	250 KCMIL-4/0 AWG
Conductor - Copper Str Size B	4/0 AWG
Conductor - Material	COPPER
Wire Size	250 KCMIL-4/0 AWG
Conductor - Copper Flex K Size A	4/0 AWG
Conductor - Copper Flex M Run	4/0 AWG
Conductor - Copper Flex M Size A	4/0 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Flex I Run	4/0 AWG
Conductor - Copper Str Size	250 KCMIL-4/0 AWG
Conductor - Copper Str Size B Range	4/0 AWG
Conductor - Copper Flex K Run	4/0 AWG
Conductor - Copper Flex I Size A	4/0 AWG



Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	1-7/16 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	76 mm
Dimension - B Length inch	1.44 in
Dimension - Length BB inch	1.30 in
Dimension - Length Overall inch	3.00 in
Dimension - Strip Length inch	1.38 in

General

Feature - Barrel Type	Standard
Feature - Barrel Style Plated	Skived Y
Color Code	Yellow, Purple
Trade Name	HYREDUCER™
Die Index	16/15
Die Index - Element A	16
Die Index - Element B	15
Die Index Run Side	16
UPC	781810415825
Color Code - Side B	Purple
Die Index Tap Side	15
Color Code - Side A	Yellow
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810415825
UPC 14 Digit GTIN	00781810415825

Logistics

Minimum Pack Quantity	25
Pallet Quantity	2250



A Hubbell brand