



YSR2CFX4CFXLTKITC, Cu Splice Reducer with Clear Heat Shrink, Barrel A: 2 Flex/AWG, Barrel B: 4 Flex/AWG

By Burndy
Catalog # YSR2CFX4CFXLTKITC

CU Splice Reducer, Barrel A 2 Flex G,H,I,K,M,DLO, 2 AWG, Barrel B 4 Flex G,H,I,K,M,DLO, 4 AWG CU, Kit includes clear heat shrink

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	2 AWG-4 AWG
Conductor - Copper Flex K Tap	4 AWG
Conductor - Copper Flex K Size A	2 AWG
Conductor - Copper Flex K Size B	4 AWG
Conductor - Copper Flex M Size B	4 AWG
Conductor - Copper Flex M Run	2 AWG
Conductor - Copper Flex M Size A	2 AWG
Conductor - Copper Str Size	2 AWG-4 AWG
Conductor - Copper Flex I Tap	4 AWG
Conductor - Copper Flex K Run	2 AWG
Conductor - Copper Flex I Size B	4 AWG



Conductor - Copper Flex G Size A	2 AWG
Conductor - Copper Flex G Size B	4 AWG
Conductor - Copper Flex G Run	2 AWG
Conductor - Copper Flex H Run	2 AWG
Conductor Size	2 AWG-4 AWG
Conductor - Copper Flex H Size A	2 AWG
Conductor - Copper Flex G Tap	4 AWG
Conductor - Copper Flex M Tap	4 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	4 AWG
Conductor - Copper Flex I Run	2 AWG
Conductor - Copper Flex H Size B	4 AWG
Conductor - Copper Flex I Size A	2 AWG

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	45 mm
Dimension - Strip Length inch	0.78 in
Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.82 in
Dimension - Length BB inch	0.74 in
Dimension - Length Overall inch	1.86 in

General

Trade Name	HYREDUCER™
Die Index	10/8
Die Index - Element A	10

Die Index - Element B	8
Die Index Run Side	10
Die Index Tap Side	8
Feature - Barrel Type	Standard
Feature - Barrel Style	Skived
Plated	Y
Color Code	Brown, Gray
Sub Brand	HYREDUCER
UPC	781810429419
Color Code - Side B	Gray
Color Code - Side A	Brown
Type	YSR-TC
Construction Material - Main	Copper
Material	Copper

Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810429419
UPC 14 Digit GTIN	00781810429419

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2250
Carton Quantity	25

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[French, English\]](#)



A Hubbell brand