



YSR2CFX6CFXLTKITC, Cu Splice Reducer with Clear Heat Shrink, Barrel A: 2 Flex/AWG, Barrel B: 6 Flex/AWG

By Burndy
Catalog # YSR2CFX6CFXLTKITC

CU Splice Reducer, Barrel A 2 Flex G,H,I,K,M,DLO, 2 AWG, Barrel B 6 Flex G,H,I,K,M,DLO, 6 AWG CU, Kit includes clear heat shrink

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	2 AWG-6 AWG
Conductor - Copper Flex K Tap	6 AWG
Conductor - Copper Flex K Size A	2 AWG
Conductor - Copper Flex K Size B	6 AWG
Conductor - Copper Flex M Size B	6 AWG
Conductor - Copper Flex M Run	2 AWG
Conductor - Copper Flex M Size A	2 AWG
Conductor - Copper Str Size	2 AWG-6 AWG
Conductor - Copper Flex I Tap	6 AWG
Conductor - Copper Flex K Run	2 AWG
Conductor - Copper Flex I Size B	6 AWG



Conductor - Copper Flex G Size A	2 AWG
Conductor - Copper Flex G Size B	6 AWG
Conductor - Copper Flex G Run	2 AWG
Conductor - Copper Flex H Run	2 AWG
Conductor Size	2 AWG-6 AWG
Conductor - Copper Flex H Size A	2 AWG
Conductor - Copper Flex G Tap	6 AWG
Conductor - Copper Flex M Tap	6 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	6 AWG
Conductor - Copper Flex I Run	2 AWG
Conductor - Copper Flex H Size B	6 AWG
Conductor - Copper Flex I Size A	2 AWG

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	50 mm
Dimension - Strip Length inch	0.78 in
Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.82 in
Dimension - Length BB inch	0.73 in
Dimension - Length Overall inch	1.96 in

General

Trade Name	HYREDUCER™
Die Index	10/7
Die Index - Element A	10

Die Index - Element B	7	Plating Type	Tin - Electro Plated
Die Index Run Side	10	Finish Type	Tin-Plated
Die Index Tap Side	7	UPC 12 Digit	781810345764
Feature - Barrel Type	Standard	UPC 14 Digit GTIN	00781810345764
Feature - Barrel Style	Skived		
Plated	Y	Logistics	
Color Code	Brown, Gray	Minimum Pack Quantity	1
Sub Brand	HYREDUCER	Pallet Quantity	2250
UPC	781810345764	Carton Quantity	25
Color Code - Side B	Blue		
Color Code - Side A	Brown	Product Assets	
Type	YSR-TC	Catalog [English]	
Construction Material - Main	Copper	Installation Manual [French, English]	
Material	Copper		

