



YSR2CFX8CFXLTKITC, Cu Splice Reducer with Clear Heat Shrink, Barrel A: 2 Flex/AWG, Barrel B: 8 Flex/AWG

By Burndy
Catalog # YSR2CFX8CFXLTKITC

CU Splice Reducer, Barrel A 2 Flex G,H,I,K,M,DLO, 2 AWG, Barrel B 8 Flex G,H,I,K,M,DLO, 8 AWG CU, Kit includes clear heat shrink

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	2 AWG-8 AWG
Conductor - Copper Flex K Tap	8 AWG
Conductor - Copper Flex K Size A	2 AWG
Conductor - Copper Flex K Size B	8 AWG
Conductor - Copper Flex M Size B	8 AWG
Conductor - Copper Flex M Run	2 AWG
Conductor - Copper Flex M Size A	2 AWG
Conductor - Copper Str Size	2 AWG-8 AWG
Conductor - Copper Flex I Tap	8 AWG
Conductor - Copper Flex K Run	2 AWG
Conductor - Copper Flex I Size B	8 AWG



Conductor - Copper Flex G Size A	2 AWG
Conductor - Copper Flex G Size B	8 AWG
Conductor - Copper Flex G Run	2 AWG
Conductor - Copper Flex H Run	2 AWG
Conductor Size	2 AWG-8 AWG
Conductor - Copper Flex H Size A	2 AWG
Conductor - Copper Flex G Tap	8 AWG
Conductor - Copper Solid Size B	6 AWG
Conductor - Copper Flex M Tap	8 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	8 AWG
Conductor - Copper Flex I Run	2 AWG
Conductor - Copper Flex H Size B	8 AWG
Conductor - Copper Flex I Size A	2 AWG

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	45 mm
Dimension - Strip Length inch	0.78 in
Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.82 in
Dimension - Length BB inch	0.60 in
Dimension - Length Overall inch	2.02 in

General

Trade Name	HYREDUCER™
------------	------------

Die Index	10/49	Material	Copper
Die Index - Element A	10	Plating Type	Tin - Electro Plated
Die Index - Element B	49	Finish Type	Tin-Plated
Die Index Run Side	10	UPC 12 Digit	781810473948
Die Index Tap Side	49	UPC 14 Digit GTIN	00781810473948
Feature - Barrel Type	Standard	Logistics	
Feature - Barrel Style	Skived	Minimum Pack Quantity	1
Plated	Y	Pallet Quantity	6000
Color Code	Brown, Red	Carton Quantity	25
Sub Brand	HYREDUCER	Product Assets	
UPC	781810473948	Catalog [English]	
Color Code - Side B	Red	Installation Manual [French, English]	
Color Code - Side A	Brown		
Type	YSR-TC		
Construction Material - Main	Copper		

