



YSR3128FXLTCKITC, Compression Splice Reducer, Barrel A 350 kcmil, Barrel B 4/0 Flex, includes clear heat shrink

By Burndy
Catalog # [YSR3128FXLTCKITC](#)

CU Splice Reducer, Barrel A 350 kcmil, Barrel B 4/0 Flex
G,H,I,K,M,DLO, 4/0 AWG CU, Kit includes clear heat shrink

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	350 KCMIL-4/0 AWG
Conductor - Copper Flex K Tap	4/0 AWG
Conductor - Copper Flex K Size	4/0 AWG
B	
Conductor - Copper Flex M Size	4/0 AWG
B	
Conductor - Copper Str Size	350 KCMIL-4/0 AWG
Conductor - Copper Flex I Tap	4/0 AWG
Conductor - Copper Flex I Size	4/0 AWG
B	
Conductor - Copper Flex G Size	4/0 AWG
B	
Conductor - Copper Str Size A	350 kcmil
Conductor Size	350 KCMIL-4/0 AWG
Conductor - Copper Flex G Tap	4/0 AWG
Conductor - Copper Flex M Tap	4/0 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	4/0 AWG



Conductor - Copper Flex H Size 4/0 AWG
B

Configuration

Connector Type STANDARD BARREL KITS

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	83 mm
mm	
Dimension - Strip Length inch	1.41 in
Dimension - B Length fraction	1-1/4 in
Dimension - B Length inch	1.25 in
Dimension - Length BB inch	1.40 in
Dimension - Length Overall	3.25 in
inch	

General

Trade Name	HYREDUCER™
Die Index	18/15
Die Index - Element A	18
Die Index - Element B	15
Die Index Run Side	18
Die Index Tap Side	15
Feature - Barrel Type	Standard
Feature - Barrel Style	Skived
Plated	Y
Color Code	Red, Purple
UPC	781810499610
Color Code - Side B	Purple
Color Code - Side A	Red
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810499610
UPC 14 Digit GTIN	00781810499610

Logistics

Minimum Pack Quantity	20
Pallet Quantity	1800
Carton Quantity	20



A Hubbell brand

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[French, English\]](#)