



YSR3129FXLTCKITC, Compression Splice Reducer, Barrel A 350 kcmil, Barrel B 250 kcmil, includes clear heat shrink

By Burndy
Catalog # YSR3129FXLTCKITC

CU Splice Reducer, Barrel A 350 kcmil, Barrel B 250 kcmil, 4/0 G,H,I,K,M,DLO CU, Kit includes clear heat shrink

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	350 KCMIL-250 KCMIL
Conductor - Copper Flex K Tap	4/0 AWG
Conductor - Copper Flex K Size B	4/0 AWG
Conductor - Copper Flex M Size B	4/0 AWG
Conductor - Copper Str Size	350 KCMIL-250 KCMIL
Conductor - Copper Flex I Tap	4/0 AWG
Conductor - Copper Flex I Size B	4/0 AWG
Conductor - Copper Str Size A	350 kcmil
Conductor Size	350 KCMIL-250 KCMIL
Conductor - Copper Flex G Tap	4/0 AWG
Conductor - Copper Flex M Tap	4/0 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	4/0 AWG

Configuration



Connector Type STANDARD BARREL KITS

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	80 mm
Dimension - Strip Length inch	1.41 in
Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.49 in
Dimension - Length BB inch	1.44 in
Dimension - Length Overall inch	3.13 in

General

Trade Name	HYREDUCER™
Die Index	18/16
Die Index - Element A	18
Die Index - Element B	16
Die Index Run Side	18
Die Index Tap Side	16
Feature - Barrel Type	Standard
Feature - Barrel Style Plated	Skived Y
Color Code UPC	Red, Yellow 781810472361
Color Code - Side B	Yellow
Color Code - Side A	Red
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810472361
UPC 14 Digit GTIN	00781810472361

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1728
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)

[Installation Manual \[French, English\]](#)



A Hubbell brand