



YSR3129FXTEL20, Compression Splice Reducer, Barrel A 350 kcmil, Barrel B 4/0 AWG Flex

By Burndy
Catalog # YSR3129FXTEL20

Cu Compression Reducer/Splice Telecom Kit, Long Barrel, 350 kcmil Str.(Brrl A), 4/0 AWG Flex(Brrl B)

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Standards - RoHS Compliance	CM
Status	
Certification - UL Listed Direct Burial	No

Conductor

Conductor - Copper Flex G Size A	4/0 AWG
Conductor - Copper Flex G Size B	4/0 AWG
Conductor - Copper Str Size A	4/0 AWG
Conductor Size	350 KCMIL-250 KCMIL
Conductor - Copper Flex H Size A	4/0 AWG
Conductor - Copper Flex G Tap	4/0 AWG
Conductor - Copper Flex M Tap	4/0 AWG
Conductor - Material	COPPER
Wire Size	350 KCMIL-250 KCMIL
Conductor - Copper Flex K Tap A	4/0 AWG
Conductor - Copper Flex K Size B	4/0 AWG
Conductor - Copper Flex K Size B	4/0 AWG
Conductor - Copper Flex M Size A	4/0 AWG
Conductor Type	CODE/FLEX



Conductor - Copper Flex H Tap B	4/0 AWG
Conductor - Copper Flex H Size B	4/0 AWG
Conductor - Copper Str Size	350 KCMIL-250 KCMIL
Conductor - Copper Flex I Tap B	4/0 AWG
Conductor - Copper Flex I Size A	4/0 AWG

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	2-1/2 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	129 mm
Dimension - B Length inch	2.51 in
Dimension - Length BB inch	2.36 in
Dimension - Length Overall inch	5.06 in

General

Feature - Barrel Type	Long
Feature - Barrel Style Plated	Skived Y
Color Code	Red, Yellow
Trade Name	HYREDUCER™
Die Index	18/16
Die Index Run Side	18
UPC	781810345276
Color Code - Side B	Yellow
Die Index Tap Side	16
Color Code - Side A	Red
Material	Copper
Plating Type	Tin - Electro Plated

Finish Type	Tin-Plated	Pallet Quantity	900
UPC 12 Digit	781810345276	Carton Quantity	10
UPC 14 Digit GTIN	00781810345276		

Logistics

Minimum Pack Quantity1



A Hubbell brand

Product Assets

- Catalog [English]
- Installation Manual [Spanish, French, English]