



YSR312CFXLTCKITC, Cu Splice Reducer with Clear Heat Shrink, Barrel A: 350 kcmil, Barrel B: 2 Flex/AWG

By Burndy
Catalog # [YSR312CFXLTCKITC](#)

CU Splice Reducer, Barrel A 350 kcmil, Barrel B 2 Flex
G,H,I,K,M,DLO, 2 AWG CU, Kit includes clear heat shrink

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	350 KCMIL-2 AWG
Conductor - Copper Flex K Size B Range	2 AWG
Conductor - Copper Flex K Tap	2 AWG
Conductor - Copper Flex K Size B	2 AWG
Conductor - Copper Flex M Size B	2 AWG
Conductor - Copper Flex M Size B Range	2 AWG
Conductor - Copper Str Size	350 KCMIL-2 AWG
Conductor - Copper Flex I Tap	2 AWG
Conductor - Copper Flex I Size B	2 AWG
Conductor - Copper Flex I Size B Range	2 AWG



Conductor - Copper Flex G Size B	2 AWG
Conductor - Copper Str Size A	350 kcmil
Conductor Size	350 KCMIL-2 AWG
Conductor - Copper Str Size A Range	350 kcmil
Conductor - Copper Flex G Size B Range	2 AWG
Conductor - Copper Flex G Tap	2 AWG
Conductor - Copper Flex M Tap	2 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	2 AWG
Conductor - Copper Flex H Size B	2 AWG
Conductor - Copper Flex H Size B Range	2 AWG

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	86 mm
Dimension - Strip Length inch	1.41 in
Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.49 in
Dimension - Length BB inch	0.82 in
Dimension - Length Overall inch	3.37 in

General

Trade Name	HYREDUCER™
Die Index	18/10
Die Index - Element A	18
Die Index - Element B	10
Die Index Run Side	18

Die Index Tap Side	10
Feature - Barrel Type	Standard
Feature - Barrel Style	Skived
Plated	Y
Color Code	Red, Brown
Sub Brand	HYREDUCER
UPC	781810345375
Color Code - Side B	Brown
Color Code - Side A	Red
Type	YSR-TC
Construction Material - Main	Copper
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated

UPC 12 Digit	781810345375
UPC 14 Digit GTIN	00781810345375

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1728
Carton Quantity	12

Operational

Temperature Rating	194
--------------------	-----

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[French, English\]](#)



A Hubbell brand