



YSR3434FXLTCKITC, Compression Splice Reducer, Barrel A 500 kcmil, Barrel 350 kcmil, includes clear heat shrink

By Burndy
Catalog # [YSR3434FXLTCKITC](#)

CU Splice Reducer, Barrel A 500 kcmil, Barrel B 350 kcmil
G,H,I,K,M,373 DLO CU, Kit includes clear heat shrink

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	500 KCMIL-350 KCMIL
Conductor - Copper Flex K Size B Range	350 kcmil
Conductor - Copper Flex K Tap	350 KCMIL
Conductor - Copper Flex K Size B	350 kcmil
Conductor - Copper Flex M Size B	350 kcmil
Conductor - Copper Flex M Size B Range	350 kcmil
Conductor - Copper Str Size	500 KCMIL-350 KCMIL
Conductor - Copper Flex I Tap	350 KCMIL
Conductor - Copper Flex I Size B	350 kcmil
Conductor - Copper Flex I Size B Range	350 kcmil
Conductor - Copper Flex G Size B	350 kcmil



Conductor - Copper Str Size A	500 kcmil
Conductor Size	500 KCMIL-350 KCMIL
Conductor - Copper Str Size B	350 kcmil
Conductor - Copper Str Size A Range	500 kcmil
Conductor - Copper Flex G Size B Range	350 kcmil
Conductor - Copper Flex G Tap	350 KCMIL
Conductor - Copper Flex M Tap	350 KCMIL
Conductor Type	FLEX
Conductor - Copper Flex H Tap	350 KCMIL
Conductor - Copper Flex H Size B	350 kcmil
Conductor - Copper Flex H Size B Range	350 kcmil

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	89 mm
mm	
Dimension - Strip Length inch	1.60 in
Dimension - B Length fraction	1-11/16 in
Dimension - B Length inch	1.69 in
Dimension - Length BB inch	1.69 in
Dimension - Length Overall	3.51 in
inch	

General

Trade Name	HYREDUCER™
Die Index	20/19
Die Index - Element A	20
Die Index - Element B	• 19 • L80
Die Index Run Side	20

Die Index Tap Side	• 19 • L80
Feature - Barrel Type	Standard
Feature - Barrel Style	Skived
Plated	Y
Color Code	Brown, Blue
UPC	781810472347
Color Code - Side B	Blue
Color Code - Side A	Brown
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810472347

UPC 14 Digit GTIN00781810472347

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1800
Carton Quantity	20

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[French, English\]](#)



A Hubbell brand