



YSR34FX28LTCKITC, Compression Splice Reducer, Barrel A 350 kcmil, Barrel B 4/0 AWG, includes clear heat shrink

By Burndy
Catalog # [YSR34FX28LTCKITC](#)

CU Splice Reducer, Barrel A 350 kcmil G,H,I,K,M,373 DLO, Barrel B 4/0 AWG CU, Kit includes clear heat shrink

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	350 KCMIL-4/0 AWG
Conductor - Copper Flex K Tap	4/0 AWG
Conductor - Copper Flex K Size A	350 kcmil
Conductor - Copper Flex K Size A Range	350 kcmil
Conductor - Copper Flex M Size A Range	350 kcmil
Conductor - Copper Flex M Run	350 KCMIL
Conductor - Copper Flex M Size A	350 kcmil
Conductor - Copper Str Size	350 KCMIL-4/0 AWG
Conductor - Copper Flex I Tap	4/0 AWG
Conductor - Copper Flex K Run	350 KCMIL
Conductor - Copper Flex G Size A	350 kcmil
Conductor - Copper Flex G Size A Range	350 kcmil



Conductor - Copper Flex G Run	350 KCMIL
Conductor - Copper Flex H Run	350 KCMIL
Conductor Size	350 KCMIL-4/0 AWG
Conductor - Copper Str Size B	4/0 AWG
Conductor - Copper Flex H Size A	350 kcmil
Conductor - Copper Flex G Tap	4/0 AWG
Conductor - Copper Flex M Tap	4/0 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	4/0 AWG
Conductor - Copper Flex I Run	350 KCMIL
Conductor - Copper Str Size B Range	4/0 AWG
Conductor - Copper Flex H Size A Range	350 kcmil
Conductor - Copper Flex H Size B Range	N/A
Conductor - Copper Flex I Size A	350 kcmil
Conductor - Copper Flex I Size A Range	350 kcmil

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	100 mm
Dimension - Strip Length inch	1.60 in
Dimension - B Length fraction	1-11/16 in
Dimension - B Length inch	1.69 in
Dimension - Length BB inch	1.30 in
Dimension - Length Overall	3.95 in
inch	

General

Trade Name	HYREDUCER™	Plating Type	Tin - Electro Plated
Die Index	19/15	Finish Type	Tin-Plated
Die Index - Element A	• 19 • L80	UPC 12 Digit	781810345160
		UPC 14 Digit GTIN	00781810345160
Die Index - Element B	15	Logistics	
Die Index Run Side	• 19 • L80	Minimum Pack Quantity	1
Die Index Tap Side	15	Pallet Quantity	1080
Feature - Barrel Type	Standard	Carton Quantity	12
Feature - Barrel Style	Skived	Operational	
Plated	Y	Temperature Rating	194
Color Code	Blue, Purple	Product Assets	
UPC	781810345160	Catalog [English]	
Color Code - Side B	Purple	Installation Manual [French, English]	
Color Code - Side A	Blue		
Material	Copper		



A Hubbell brand