



YSR34FX29FXLTCKITC, Compression Splice Reducer, Barrel A 350 kcmil, Barrel B 250 kcmil, includes clear heat shrink

By Burndy
Catalog # [YSR34FX29FXLTCKITC](#)

CU Splice Reducer, Barrel A 350 kcmil G,H,I,K,M,373 DLO, Barrel B 250 kcmil, 4/0 G,H,I,K,M,DLO CU, Kit includes clear heat shrink

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	350 KCMIL-250 KCMIL
Conductor - Copper Flex K Size	4/0 AWG
B Range	
Conductor - Copper Flex K Tap	4/0 AWG
Conductor - Copper Flex K Size	350 kcmil
A	
Conductor - Copper Flex K Size	4/0 AWG
B	
Conductor - Copper Flex K Size	350 kcmil
A Range	
Conductor - Copper Flex M Size	4/0 AWG
B	
Conductor - Copper Flex M Size	350 kcmil
A Range	
Conductor - Copper Flex M Size	4/0 AWG
B Range	
Conductor - Copper Flex M Run	350 KCMIL



Conductor - Copper Flex M Size	350 kcmil
A	
Conductor - Copper Str Size	350 KCMIL-250 KCMIL
Conductor - Copper Flex I Tap	4/0 AWG
Conductor - Copper Flex K Run	350 KCMIL
Conductor - Copper Flex I Size	4/0 AWG
B	
Conductor - Copper Flex G Size	350 kcmil
A	
Conductor - Copper Flex G Size	350 kcmil
A Range	
Conductor - Copper Flex G Run	350 KCMIL
Conductor - Copper Flex H Run	350 KCMIL
Conductor Size	350 KCMIL-250 KCMIL
Conductor - Copper Flex H Size	350 kcmil
A	
Conductor - Copper Flex G Tap	4/0 AWG
Conductor - Copper Flex M Tap	4/0 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	4/0 AWG
Conductor - Copper Flex I Run	350 KCMIL
Conductor - Copper Flex H Size	350 kcmil
A Range	
Conductor - Copper Flex H Size	N/A
B Range	
Conductor - Copper Flex I Size	350 kcmil
A	
Conductor - Copper Flex I Size	350 kcmil
A Range	

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	97 mm
mm	
Dimension - Strip Length inch	1.60 in

Dimension - B Length fraction	1-11/16 in	Color Code - Side B	Yellow
Dimension - B Length inch	1.69 in	Color Code - Side A	Blue
Dimension - Length BB inch	1.44 in	Material	Copper
Dimension - Length Overall inch	3.81 in	Plating Type	Tin - Electro Plated
		Finish Type	Tin-Plated
		UPC 12 Digit	781810472354
		UPC 14 Digit GTIN	00781810472354
General		Logistics	
Trade Name	HYREDUCER™	Minimum Pack Quantity	1
Die Index	19/16	Pallet Quantity	864
Die Index - Element A	19 - L80	Carton Quantity	6
Die Index - Element B	16		
Die Index Run Side	19 - L80		
Die Index Tap Side	16		
Feature - Barrel Type	Standard		
Feature - Barrel Style	Skived		
Plated	Y		
Color Code	Blue, Yellow		
UPC	781810472354		
		Operational	
		Temperature Rating	194
		Product Assets	
		Catalog [English]	
		Installation Manual [French, English]	

