



YSR34FX29FXTEL24, Compression Splice Reducer, Barrel A 350 kcmil, Barrel B 4/0 AWG Flex

By Burndy
Catalog # [YSR34FX29FXTEL24](#)

In-line Reducer splice

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
Certification - UL Listed Direct Burial	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Flex G Size A	350 kcmil
Conductor - Copper Flex G Size A Range	350 kcmil
Conductor - Copper Flex G Run	350 KCMIL
Conductor - Copper Flex H Run	350 KCMIL
Conductor Size	350 KCMIL-250 KCMIL
Conductor - Copper Str Size B	4/0 AWG
Conductor - Copper Flex H Size A	350 kcmil
Conductor - Copper Flex G Size B Range	4/0 AWG
Conductor - Copper Flex G Tap	4/0 AWG
Conductor - Copper Flex M Tap	4/0 AWG
Conductor - Material	COPPER
Wire Size	350 KCMIL-250 KCMIL
Conductor - Copper Flex K Size B Range	4/0 AWG



Conductor - Copper Flex K Tap	4/0 AWG
Conductor - Copper Flex K Size A	350 kcmil
Conductor - Copper Flex K Size B	4/0 AWG
Conductor - Copper Flex K Size A Range	350 kcmil
Conductor - Copper Flex M Size B	4/0 AWG
Conductor - Copper Flex M Size A Range	350 kcmil
Conductor - Copper Flex M Size B Range	4/0 AWG
Conductor - Copper Flex M Run	350 KCMIL
Conductor - Copper Flex M Size A	350 kcmil
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	4/0 AWG
Conductor - Copper Flex I Run	350 KCMIL
Conductor - Copper Str Size	350 KCMIL-250 KCMIL
Conductor - Copper Flex H Size A Range	350 kcmil
Conductor - Copper Flex H Size B Range	4/0 AWG
Conductor - Copper Flex I Tap	4/0 AWG
Conductor - Copper Flex K Run	350 KCMIL
Conductor - Copper Flex I Size B	4/0 AWG
Conductor - Copper Flex I Size A	350 kcmil
Conductor - Copper Flex I Size B Range	4/0 AWG
Conductor - Copper Flex I Size A Range	350 kcmil

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	2-3/4 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	147 mm
Dimension - B Length inch	2.75 in
Dimension - Length BB inch	2.36 in
Dimension - Length Overall inch	5.78 in
Dimension - Strip Length inch	2.67 in

General

Feature - Barrel Type	Long
Feature - Barrel Style	Skived
Plated	Y
Color Code	Blue, Yellow
Trade Name	HYREDUCER™
Die Index	19/16
Die Index Run Side	• 19 • L80
UPC	781810345054

Color Code - Side B	Yellow
Die Index Tap Side	16
Color Code - Side A	Blue
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810345054
UPC 14 Digit GTIN	00781810345054

Logistics

Minimum Pack Quantity	6
Pallet Quantity	540
Carton Quantity	6

Operational

Temperature Rating	194
--------------------	-----

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[Spanish, French, English\]](#)



A Hubbell brand