



YSR3934FXLTCKITC, Compression Splice Reducer, Barrel A 750 kcmil, Barrel B 350 kcmil, includes clear heat shrink

By Burndy
Catalog # YSR3934FXLTCKITC

CU Splice Reducer, Barrel A 750 kcmil, Barrel B 350 kcmil
G,H,I,K,M,373 DLO CU, Kit includes clear heat shrink

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Buy American Compliant	No
Certification - cULus	No
EU RoHS Indicator	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	750 KCMIL-350 KCMIL
Conductor - Copper Flex K Size B Range	350 kcmil
Conductor - Copper Flex K Tap	350 KCMIL
Conductor - Copper Flex K Size B	350 kcmil
Conductor - Copper Flex M Size B	350 kcmil
Conductor - Copper Flex M Size B Range	350 kcmil
Conductor - Copper Str Size	750 KCMIL-350 KCMIL
Conductor - Copper Flex I Tap	350 KCMIL
Conductor - Copper Flex I Size B	350 kcmil
Conductor - Copper Flex I Size B Range	350 kcmil



Conductor - Copper Flex G Size B	350 kcmil
Conductor - Copper Str Size A	750 kcmil
Conductor Size	750 KCMIL-350 KCMIL
Conductor - Copper Str Size B	350 kcmil
Conductor - Copper Str Size A Range	750 kcmil
Conductor - Copper Flex G Size B Range	350 kcmil
Conductor - Copper Flex G Tap	350 KCMIL
Conductor - Copper Flex M Tap	350 KCMIL
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	350 KCMIL
Conductor - Copper Flex H Size B	350 kcmil
Conductor - Copper Flex H Size B Range	350 kcmil

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	104 mm
Dimension - Strip Length inch	1.67 in
Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.78 in
Dimension - Length BB inch	1.69 in
Dimension - Length Overall	4.09 in
inch	

General

Trade Name	HYREDUCER™
Die Index	24/19
Die Index - Element A	24
Die Index - Element B	• 19
Finish Type	Tin-Plated

Die Index Run Side	24 L80
Die Index Tap Side	• 19 • L80
Feature - Barrel Type	Standard
Feature - Barrel Style	Skived
Plated	Y
Color Code	Black, Blue
Sub Brand	HYREDUCER
UPC	781810472309
Color Code - Side B	Blue
Color Code - Side A	Black
Type	YSR-TC
Construction Material - Main	Copper
Material	Copper
Plating Type	Tin - Electro Plated

UPC 12 Digit	781810472309
UPC 14 Digit GTIN	00781810472309

Logistics

Minimum Pack Quantity	1
Pallet Quantity	864
Carton Quantity	6

Operational

Temperature Rating	194
--------------------	-----

Product Assets

- [Catalog \[English\]](#)
- [Installation Manual \[French, English\]](#)



A Hubbell brand