



YSR3938FXLTCKITC, Compression Splice Reducer, Barrel A 750 kcmil, Barrel B 500 kcmil, includes clear heat shrink

By Burndy
Catalog # [YSR3938FXLTCKITC](#)

CU Splice Reducer, Barrel A 750 kcmil, Barrel B 500 kcmil H,I,K / 550 kcmil G,H,I,535 DLO CU, Kit includes clear heat shrink

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	750 KCMIL-500 KCMIL-550 KCMIL
Conductor - Copper Flex K Size B Range	500 kcmil
Conductor - Copper Flex K Tap	500-550 KCMIL
Conductor - Copper Flex K Size B	500 kcmil
Conductor - Copper Flex M Size B	500 kcmil
Conductor - Copper Flex M Size B Range	500 kcmil
Conductor - Copper Str Size	750 KCMIL-500 KCMIL-550 KCMIL
Conductor - Copper Flex I Tap	500-550 KCMIL
Conductor - Copper Flex I Size B	500 kcmil
Conductor - Copper Flex I Size B Range	500 kcmil



Conductor - Copper Flex G Size B	500 kcmil
Conductor - Copper Str Size A	750 kcmil
Conductor Size	750 KCMIL-500 KCMIL-550 KCMIL
Conductor - Copper Str Size B	500 kcmil
Conductor - Copper Str Size A Range	750 kcmil
Conductor - Copper Flex G Size B Range	500 kcmil
Conductor - Copper Flex G Tap	500-550 KCMIL
Conductor - Copper Flex M Tap	500-550 KCMIL
Conductor Type	CODE/FLEX
Conductor - Copper Flex H Tap	500-550 KCMIL
Conductor - Copper Flex H Size B	500 kcmil
Conductor - Copper Flex H Size B Range	500 kcmil

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	96 mm
Dimension - Strip Length inch	1.67 in
Dimension - B Length fraction	1-3/4 in
Dimension - B Length inch	1.78 in
Dimension - Length BB inch	1.88 in
Dimension - Length Overall inch	3.79 in

General

Trade Name	HYREDUCER™
Die Index	24/L99
Die Index - Element A	24

Die Index - Element B	L99
Die Index Run Side	24
Die Index Tap Side	L99
Feature - Barrel Type	Standard
Feature - Barrel Style	Skived
Plated	Y
Color Code	Black, Pink
UPC	781810472293
Color Code - Side B	Pink
Color Code - Side A	Black
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810472293

UPC 14 Digit GTIN00781810472293

Logistics

Minimum Pack Quantity	1
Pallet Quantity	864
Carton Quantity	6

Operational

Temperature Rating	194
--------------------	-----

Product Assets

- Catalog [English]
- Installation Manual [French, English]



A Hubbell brand