



YSR44FX29FXLTCKITC, Compression Splice Reducer, Barrel A 750 kcmil, Barrel B 250 kcmil, includes clear heat shrink

By Burndy
Catalog # [YSR44FX29FXLTCKITC](#)

CU Splice Reducer, Barrel A 750 kcmil G,H,777 DLO, Barrel B 250 kcmil, 4/0 G,H,I,K,M,DLO CU, Kit includes clear heat shrink

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	750 KCMIL-250 KCMIL
Conductor - Copper Flex K Size B Range	4/0 AWG
Conductor - Copper Flex K Tap	4/0 AWG
Conductor - Copper Flex K Size A	750 KCMIL
Conductor - Copper Flex K Size B	4/0 AWG
Conductor - Copper Flex K Size A Range	750 KCMIL
Conductor - Copper Flex M Size B	4/0 AWG
Conductor - Copper Flex M Size A Range	750 KCMIL
Conductor - Copper Flex M Size B Range	4/0 AWG
Conductor - Copper Flex M Run	750 KCMIL



Conductor - Copper Flex M Size A	750 KCMIL
Conductor - Copper Str Size	750 KCMIL-250 KCMIL
Conductor - Copper Flex I Tap	4/0 AWG
Conductor - Copper Flex K Run	750 KCMIL
Conductor - Copper Flex I Size B	4/0 AWG
Conductor - Copper Flex G Size A	750 kcmil
Conductor - Copper Flex G Size A Range	750 kcmil
Conductor - Copper Flex G Run	750 KCMIL
Conductor - Copper Str Size A	750 kcmil
Conductor - Copper Flex H Run	750 KCMIL
Conductor Size	750 KCMIL-250 KCMIL
Conductor - Copper Str Size B	4/0 AWG
Conductor - Copper Flex H Size A	750 kcmil
Conductor - Copper Str Size A Range	750 kcmil
Conductor - Copper Flex G Tap	4/0 AWG
Conductor - Copper Flex M Tap	4/0 AWG
Conductor Type	FLEX
Conductor - Copper Flex H Tap	4/0 AWG
Conductor - Copper Flex I Run	750 KCMIL
Conductor - Copper Str Size B Range	4/0 AWG
Conductor - Copper Flex H Size A Range	750 kcmil
Conductor - Copper Flex I Size A	750 KCMIL
Conductor - Copper Flex I Size A Range	750 KCMIL

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in

Package Width	0.000 in	UPC	781810472286
Dimension - L Length Overall mm	135 mm	Color Code - Side B	Yellow
Dimension - Strip Length inch	1.96 in	Color Code - Side A	Yellow
Dimension - B Length fraction	2-1/16 in	Material	Copper
Dimension - B Length inch	2.09 in	Plating Type	Tin - Electro Plated
Dimension - Length BB inch	1.44 in	Finish Type	Tin-Plated
Dimension - Length Overall inch	5.33 in	UPC 12 Digit	781810472286
		UPC 14 Digit GTIN	00781810472286
General		Logistics	
Trade Name	HYREDUCER™	Minimum Pack Quantity	1
Die Index	L115/16	Pallet Quantity	396
Die Index - Element A	L115	Carton Quantity	12
Die Index - Element B	16		
Die Index Run Side	L115	Operational	
Die Index Tap Side	16	Temperature Rating	194
Feature - Barrel Type	Standard	Product Assets	
Feature - Barrel Style	Skived	Catalog [English]	
Plated	Y	Installation Manual [French, English]	
Color Code	Yellow, Yellow		



A Hubbell brand